

Description

Mineral reinforced compound for injection moulding

Property, Test Condition	Standard	Unit	Values
Mechanical Properties			
Flexural Strength, 23 °C	ISO 178	MPa	50
Flexural Modulus, 23 °C	ISO 178	MPa	1800
Izod Notched Impact Strength, 23 °C	ISO 180/A	kJ/m ²	6
Izod Unnotched, 23 °C	ISO 180/U	kJ/m ²	NB
Charpy Notched Impact Strength, 23° C	ISO 179/1eA	kJ/m ²	
Charpy Unnotched, 23 °C / -30 °C	ISO 179/1eU	kJ/m ²	
Tensile Stress at Yield, 23 °C	ISO 527	MPa	30
Tensile Strain at Yield, 23 °C	ISO 527	%	12
Tensile Stress at Break, 23 °C	ISO 527	MPa	5
Tensile Strain at Break, 23 °C	ISO 527	%	>30
Tensile Modulus, 23 °C	ISO 527	MPa	2050
Ball Indentation Hardness, 23 °C	ISO 2039-1	N/mm ²	84 / HB 358N
Thermal Properties			
Vicat Softening Temperature VST/B/50 (50N, 50 °C/h)	ISO 306	°C	
Heat Deflection Temperature A; (1.8 MPa) *	ISO 75	°C	51
Heat Deflection Temperature B; (0.45 MPa)	ISO 75	°C	82
Other Properties			
Density	ISO 1183	g/cm ³	1,36
Melt Flow Rate [190 °C& 2.16 kg / 200 °C/ 5 kg]	ISO 1133	g/10 min	11 / 41

Typical values for uncolored products. The properties stated above are not for specification purposes.

* Mold temperature 30°C

Processing

ArcBiox™ materials must be always dried before processing with dehumidifying dryer, due to fact that insufficient drying before processing will cause loss of mechanical properties. Please note that a combination of a very long drying time and high temperature may cause degradation and agglomeration of pellets and may cause yellowing.

Property, Test Condition	Standard	Unit	Values
Processing			
Linear Mold Shrinkage (Note 2.)	ISO 294-4	%	
Melt Temperature Range		°C	180-200
Feed Throat		°C	30-50
Feed Temperature		°C	170-190
Compression Section		°C	180-200
Metering Section		°C	180-200
Nozzle		°C	180-200
Mold Temperature Range; cooling time according to part		°C	20-40
Injection Velocity		mm/s	medium
Back Pressure		bar	10-20
Drying Temperature, Dew point -40°C (Note 1.)		°C	80
Drying Time		h	5

Note 1. Moisture content less than 0.025% (250 ppm) is recommended to prevent loss of mechanical properties.

Note 2. Shrinkage value is measured from test part (4x70x150mm) that is moulded at 30 °C mould temperature.

Change-over point should be always checked visually by setting holding pressure to 0 bar/MPa to avoid over filling and flashes. Part should be 95 – 98% filled before changing to holding pressure.

Use low MFR Polypropylene to clean the screw and barrel.

DISCLAIMER: The product(s) mentioned herein are not intended and are restricted to be used for medical, pharmaceutical or healthcare applications. Determining the suitability of these materials for any applications, complying with legal requirements for any such applications, are the sole responsibility and obligation of anyone purchasing these materials for such applications. The information in this Data Sheet is given according to our best knowledge at the date shown in footer. The information is guidance for safe handling, use, processing and storage. This data sheet is for informative purpose only and all specifications need to be discussed and agreed with Arctic Biomaterials Oy separately.

ARCTIC BIOMATERIALS OY MAKES NO WARRANTY, EXPRESS OR IMPLIED, REGARDING THE INFORMATION CONTAINED HEREIN OR ITS PRODUCTS, INCLUDING BUT NOT LIMITED TO ANY WARRANTY AS TO ACCURACY OR COMPLETENESS OF INFORMATION, OR ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.